

받 0362

USER INSTRUCTIONS

C € 2575

Product Ref: PRO-230 – 18-gauge RazorPlex, water-based PU / nitrile foam palm coated

glove. Cut B

Sizes available: 8, 9, 10 and 11

These products are classed as Personal Protective Equipment (PPE) by the UK 2019 S1696 Schedule 35 Regulation 38 and Regulation 2016/425 on PPE as brought into UK Law and Amended. They have been shown to comply with these Regulations through the Harmonized Standards BS EN 388:2016, BS EN 420:2003+AI:2009 and Designated Standards BS EN 388:2016, BS EN 420:2003+AI:2009.

Manufacturer: Treadstone Products Unit 36, Abenbury Way, Wrexham Industrial Estate Wrexham, UK, LLI3 9UZ

Tel: +44(0) 1978 664667

E-mail: info@treadstoneproducts.com

www.treadstoneproducts.com

Approval Body:

ITS Testing Services (UK) Ltd

Centre Court

Meridian Business Park

Leicester

LEI9 IWD, UK

Tel: +44 (0)II6 263 0330 www.intertek.com

(AB0362)

Notified Body: INTERTEK ITALIA SPA,

Via Guido Miglioli, 2/A – 20063

. Cernusco sul Naviglio,

(MI), Italia

www.intertek.com

(Notified Body: 2575)

Care: Before removal, gloves should be cleared of any contamination.

Storage: When not in use, store the product in a dry place away from direct sunlight, sources of contamination and extremes of temperature. Handling: New and used gloves should be thoroughly checked for signs of wear or damage (e.g. cuts or holes) before use. Do not use damaged gloves.

Performance and limitation of use – This product has been tested in accordance with: BS EN 388:2016, BS EN 420:2003+Al:2009 (See table below)


BS EN 420:2003+Al:2009: Dexterity level 5

BS EN 388:2016:

Tested in	Requirement	Level
accordance with EN 388:2016	(6.1) Abrasion resistance	4
	(6.2) Blade cut resistance	X
	(6.4) Tear resistance	4
	(6.5) Puncture resistance	2
	(6.3) TDM Cut resistance	В
4 X 4 2 B	(6.6) Impact protection	

X: indicates that the glove has not been tested

EN 388:2016



EN 388:2016 Levels are based on the table below:

TEST		LEVEL I	LEVEL 2	LEVEL 3	LEVEL 4	LEVEL 5		
6.1 Abrasion resistance (number of rubs)		100	500	2000	8000	-		
6.2 Coupe test: Blade cut resistance (index) ^{1,2}		1.2	2.5	5.0	10.0	20.0		
6.4 Tear resistance (N)		10	25	50	75	-		
6.5 Puncture resistance (N) ³		20	60	100	150	-		
Levels of performance for materials tested with EN ISO 13997								
TEST	LEVEL A	LEVEL B	LEVEL C	LEVEL D	LEVEL E	LEVEL F		
6.3 TDM: cut resistance (N) ^{1, 2}	2	5	10	15	22	30		
Levels of performance tested according to EN 13594:2015, 6.9 with impact energy of 5 J								
TEST	PASS		NOT TESTED / FAIL					
Impact protection ⁴	P <bla< td=""><td colspan="4">ANK> - No code or text is added if not tested or test failed</td></bla<>		ANK> - No code or text is added if not tested or test failed					

Test results relate to the palm area of the glove unless otherwise stated

NOTE I: For dulling during the cut resistance test (6.2), the coupe test results are only indicative while the TDM cut resistance test (6.3) is the reference performance result.

NOTE 2: There is no correlation between the levels of performance obtained with the 6.2 and 6.3 test methods.

NOTE 3: Gloves meeting the requirements for resistance to puncture may NOT be suitable for protection against sharply pointed objects such as hypodermic needles.

NOTE 4: Each area where impact protection is claimed shall be tested. Due to the test method (test specimen dimensions), protection against impacts on fingers cannot be tested. When the requirements of the impact test are fulfilled by the gloves, the marking code 'P' is added after the five performance levels number, otherwise no code is added.

Notes:

- (a) Gloves are made of HPPE with steel, dipped in water-based PU / nitrile foam.
- (b) Protection is limited to part of the hand only.
- (c) Gloves are designated for protection against mechanical risks. Cat II Intermediate risk only. See performance data.
- (d) Not suitable for use where there is a risk of entanglement (for example near moving machinery), chemical risk or electrical risk.
- (e) These gloves are not suitable for washing. Do not launder or wash. Gloves can be cleaned using a damp cloth or similar.
- (f) Some gloves may contain ingredients, such as natural rubber latex and accelerators which could potentially cause irritation / allergic reaction. In case of any adverse reaction / irritation, seek medical advice.
- (g) Retain these instructions for future reference.

For further information, user instructions, DofC or details of our full range, scan here:

Product made in China